




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD



NOTE:

- 1. Only for reference, could be used on single to 5 cores cable.
- 2. L is 500mm for standard kits. It could be adjusted for actual usage.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ARJUN G. 31MAY2023		<div></div> TE Connectivity						
		CHK MARTIN 31MAY2023								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±		APVD MARTIN 31MAY2023		NAME 1.8/3kV NON-SHIELDED CABLE JOINT				
				PRODUCT SPEC -		-				
MATERIAL TBD		APPLICATION SPEC -		SIZE				CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT -		A3		00779	©-APKJ-3_CORE	-		
				CUSTOMER DRAWING				SCALE 1:2	SHEET 1 OF 1	REV 1