


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - K. MUNZ ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE	13JUN2018	GK	KM



LABEL ACROSS: 7
LABELS PER SHEET: 133
LABELS PER PACK: 1330
SHEETS PER PACK: 10

All dimensions in INCHES[mm]

TE PN: 598230-000

MATERIAL	PE200-LASER PRINTABLE POLYESTER, MATTE SILVER
ADHESIVE TYPE	ACRYLIC PERMANENT
LINER	WHITE KRAFT
PRINT	BLACK COLOUR

TOLERANCES INCH [mm] LABEL HEIGHT: ±.012 [0.3] LABEL WIDTH: ±.012 [0.3] WEB WIDTH: ±.031 [0.8] VERTICAL REPEAT: ±.031 [0.8]* HORIZONTAL REPEAT: ±.031 [0.8]* PRINT POSITIONING: ±.031 [0.8]* LEFT MARGIN: ±.016 [0.4] QUANTITY: -0 % +2 % *NON ACCUMULATING		THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: INCHES [mm] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		DWN 13JUN2018 CHK 13JUN2018 K. MUNZ APVD 13JUN2018 K. MUNZ PRODUCT SPEC TTDS-070 APPLICATION SPEC		TE TE Connectivity Ltd. NAME LM - METALLIZED POLYESTER LABELS ON SHEET	
MATERIAL SEE TABLE		FINISH -		WEIGHT 0.12g		SIZE A2 C2290 C=307-LM	
CUSTOMER DRAWING				SCALE NTS		SHEET 1 of 1 REV A	