

4

3

2

1


© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	NEW DRAWING	28AUG2020	GSK	AMO

D

D



NOTES

- DIMENSIONS IN mm. a = AS SUPPLIED, b = AFTER FREE RECOVERY
- STANDARD LENGTHS L: 1000 mm, 1500 mm. OTHER CUT LENGTHS AVAILABLE UNDER REQUEST.
- MAXIMUM LONGITUDINAL CHANGE AFTER FREE RECOVERY: -5%
- STANDARD CUT LENGTH TOLERANCES:
  - ± 5 mm (P ≤ 500)
  - ± 10 mm (P < 1000)
  - ± 15 mm (P < 1500)
  - ± 1% (P > 1500)
- STANDARD PRINTING: PRODUCT SIZE

C

C

B

B

PRODUCT SIZE	APPLICATION RANGE (MM)		Ha NOM	Fa NOM	W	
	DIAMETER				a MIN	b MIN
	MIN.	MAX.				
45/8	8	45	180	20	1.1	3
55/12	12	55	215	20	1.1	3
84/15	15	84	305	20	1.1	3
100/25	25	100	365	20	1.1	3
125/30	30	125	435	20	1.1	3
146/34	34	146	515	20	1.1	3
164/42	42	164	560	20	1.1	3
200/50	50	200	690	20	1.1	3



A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 28AUG2020	TE Connectivity		
DIMENSIONS: mm		CHK AMO 28AUG2020			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD AMO 28AUG2020	NAME CNSM REINFORCED WRAPAROUND SLEEVES		
		PRODUCT SPEC —	SIZE A3		
MATERIAL —		APPLICATION SPEC —	CAGE CODE 00779	DRAWING NO EPD-202-311926-01	RESTRICTED TO —
FINISH —		WEIGHT —	SCALE NTS		SHEET 1 of 1
CUSTOMER DRAWING			REV 1		