



LOG		DIST		REV		REVISIONS		DATE	APPD
LOC	NO	ZONE	LTR	NO	DATE	DESCRIPTION	DATE		
G	14					A REVISED PER 0720-0230-93	2/28/93		DAP



METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
16-14 AWG STRANDED	16-14 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

STAMP AMP 16-14# APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		31442 PART NO	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE		COPPER PER ASTM B-152 ANNEALED		AMP Incorporated Harrisburg, PA 17105-3808	
		WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS STRANDED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727		NAME TERMINAL, RING TONGUE, BUDGET	
		THIS DRAWING IS A CONTROLLED DOCUMENT AND SHOULD BE KEPT IN THE ORIGINAL FORM AND SUBJECT TO CHANGE. IT IS SUBJECT TO CHANGE WITHOUT NOTICE FOR THE LATEST REVISION.		APPLICATION SPEC -		SIZE C 00779 C-31442	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111			WEIGHT -		SCALE 10:1	
FOR ORDER ENTRY	1-800-526-5142					SHEET 1 OF 1	

CUSTOMER DRAWING