

4

3

2

1

THIS DRAWING IS UNPUBLISHED DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION LIBRE A LA DIFFUSION

© COPYRIGHT- TE CONNECTIVITY

ALL RIGHTS RESERVED

REVISIONS

REV	DESCRIPTION /MODIFICATIONS	DATE	DWN	APVD
1	NEW DRAWING	06APR2020		GS

Features

Shrink Ratio	3:1
Temperature range	-40°C to +135°C
Flammability (IEC 60684-2 method A)	Self-extinguishing 60 sec. max.
Color	Black
Delivery Form	on spools, uncoated

Size	Inside Diameter		Recovered wall thickness* After heating	Spool Qty - Black (meters)	Spool Qty - Green/ Yellow (meters)	Ordering Description
	Minimum expanded as supplied	Maximum recovered after heating				
1.6/0.8	1.6 (0.062)	0.8 (0.031)	0.45 ± 0.12	10.0	-	CGPT-R-1.6-col code
2.4/1.2	2.4 (0.093)	1.2 (0.046)	0.50 ± 0.12	10.0	-	CGPT-R-2.4-col code
3.2/1.6	3.2 (0.125)	1.6 (0.062)	0.50 ± 0.12	10.0	5.0	CGPT-R-3.2-col code
4.8/2.4	4.8 (0.187)	2.4 (0.093)	0.50 ± 0.12	9.0	-	CGPT-R-4.8-col code
6.4/3.2	6.4 (0.250)	3.2 (0.125)	0.65 ± 0.15	8.0	3.5	CGPT-R-6.4-col code
9.5/4.8	9.5 (0.375)	4.8 (0.187)	0.65 ± 0.15	6.0	3.0	CGPT-R-9.5-col code
12.7/6.4	12.7 (0.500)	6.4 (0.250)	0.65 ± 0.15	6.0	2.5	CGPT-R-12.7-col code
19/9.5	19.0 (0.748)	9.5 (0.375)	0.75 ± 0.15	5.0	2.0	CGPT-R-19.0-col code
25.4/12.7	25.4 (1.000)	12.7 (0.500)	0.90 ± 0.20	3.0	1.5	CGPT-R-25.4-col code

KIT CONTAINS SIZES INDICATED BY

CGPT-R-KIT-2

*Wall thickness will be less if tubing recovery is restricted during shrinkage.

CGPT 3:1 Product dimensions

Size	Inside Diameter		Recovered wall thickness* After heating	Spool Qty - (meters)	Ordering Description
	Minimum expanded as supplied	Maximum recovered after heating			
3/1	3.0 (0.118)	1.0 (0.040)	0.55 ± 0.12	10.0	CGPT-R-3/1-col code
6/2	6.0 (0.236)	2.0 (0.079)	0.65 ± 0.12	7.0	CGPT-R-6/2-col code
9/3	9.0 (0.354)	3.0 (0.118)	0.75 ± 0.15	5.0	CGPT-R-9/3-col code
12/4	12.0 (0.472)	4.0 (0.157)	0.75 ± 0.15	4.0	CGPT-R-12/4-col code
18/6	18.0 (0.709)	6.0 (0.236)	0.85 ± 0.15	3.0	CGPT-R-18/6-col code
24/8	24.0 (0.945)	8.0 (0.315)	1.00 ± 0.20	3.0	CGPT-R-24/8-col code

KIT CONTAINS SIZES INDICATED BY (black only)

CGPT-R-KIT-1

*Wall thickness will be less if tubing recovery is restricted during shrinkage.

Ordering information

Color	Standard	Black (-0) Red (-2) Yellow (-4) Blue (-6)
Size Selection	Always order the largest size that will shrink snugly over the component to be covered	
Standard packaging	On mini spools	
Ordering description	See above for description	

Product Facts

- Easy to store
- Easy to dispense
- Well-suited for repairs
- Single wall and adhesive lined tubings
- Wide variety of colors, sizes and kits available
- Also available are RaySpool kits comprised of 6 sizes and supplied with a mounting rack
- Stand alone racks and Packaging sets also available
- RoHS compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

MATERIAL

FINISH

DWM

CHK GREG S

APVD GREG S

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

WSMB

SIZE

A3

CAGE CODE

-

DRAWING NO

EPD-202-32013-01

RESTRICTED TO

-

SCALE NTS

SHEET 1 OF 2

REV 1