




 WIRE RANGE	 E13288 Listed	 LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG STRANDED	22-16 AWG SOLID OR STRANDED

- 1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC SAE AS7928
COMMERCIAL WIRE RANGE IS 22-16.
 - 2 WIRE INSULATION DIA: $\varnothing 2.032-3.175[\varnothing .080-.125]$.
 - 3 BODY MATERIAL THK: $0.787 \pm 0.051[.031 \pm .002]$.
 - 4 APPLIES FROM EDGE OF METAL WIRE BARREL TO
CENTER OF STUD HOLE.
 - 5 UL LISTED
 - 6 CSA CERTIFIED
 - 7 MATERIAL:
BODY & SLEEVE - COPPER PER ASTM B152
INSULATION - NYLON
 - 8 FINISH:
BODY & SLEEVE - TIN PLATE $0.00254[.000100]$ MIN EXT THK PER ASTM B545
INSULATION COLOR - RED

 	-	100	LOOSE PIECE, BOX	8-320571-1
 	-	5000	ON TAPE, REEL	2-320571-2
 	MS25036-150 CLASS 1	1000	LOOSE PIECE	320571
	MILITARY P/N AND CLASS	QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 9/8/93 CHK RE HERSEY 9/8/93 APVD ML ELLIS 9/8/93 PRODUCT SPEC UL 486A-B 5 APPLICATION SPEC 114-2157 WEIGHT - CUSTOMER DRAWING		TE TE Connectivity Ltd. NAME TERMINAL, RING TONGUE, PIDG™, WIRE SIZE: 22-16 AWG - SIZE A3 CAGE CODE 00779 DRAWING NO C=320571 RESTRICTED TO - SCALE NTS SHEET 1 OF 2 REV AC			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:					
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		VOLTAGE RATING: 300 V MAX		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .127[.005] 4 PLC ± - ANGLES ± -					
FOR ORDER ENTRY		1-800-526-5142		CIRCULAR MIL AREA: 0.26-1.65mm² [509-3,260] CIR MILS SOLID OR STRANDED		MATERIAL 7		FINISH 8			

