

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			O	REV & REDRAWN PER G-5651	04/27/92	DKS	DAP

D

C


B

A




- △1 STAMP AMP 20-16HD* APPROX AS SHOWN
- △2 TIN PLATE 0.00381 [0.000150] MIN THK PER ASTM B-545

AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
22-16HD AWG STRANDED	22-16HD AWG STRANDED	22-16HD AWG STRANDED



34971

PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 04/27/92 DK SCHRUM		 Tyco Electronics Corporation Harrisburg, PA 17105-3608								
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		CHK 4/27/92 D PATTERSON		NAME TERMINAL BODY, RING TONGUE - -							
		FOR APPLICATION TOOLING ASSISTANCE CENTER 1-800-722-1111		APVD 4/27/92 JL MECKLEY PRODUCT SPEC UL - 486 A APPLICATION SPEC NOT AVAILABLE															
TOOLING INFORMATION		1-800-722-1111		CIRCULAR MIL AREA: [1,186-2,426] STRANDED		MATERIAL COPPER ASTM B-152		FINISH TIN PLATE 		WEIGHT -		SIZE A2		CAGE CODE 00779		DRAWING NO C-34971		RESTRICTED TO -	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1		REV 0	