



Technical Data:

Case Material	PA GF black/yellow
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	to 32VDC
Duty Rating	2x250A
Overload	2x500A-180sec.
.....	2x1000A-30sec.
Sealing	IP 67/ IEC 529
Vibration	10G, 5-200Hz/4G, 200-2000Hz
Shock G-Level	50G/ 11ms
Duty Shock-6000Zyklen	40G/ 6ms
Weight	ca.400g/ 0.85 Pound
Temperature Range	-40°C to +85°C
Wire Section (At Nominal Load)	min. 70mm ²
Mounting position	optional
Switch lever	removeable
Max. Torque (Main Contacts)	15-20Nm
Switch lever Spare Part No.	35.200.014

	Date	Name	mm ←	Scale 1:2		Drawing No: 35-222
Drawn	25.09.2008	Seeger	General Tolerances DIN ISO 2768 mK			NSN: Liebherr-Idt.No.: 10012119
Check	25.09.2008	Grind				