

4





3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,1997 .  
 © COPYRIGHT 1997 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS	-		A	RELEASED ECN(FC00-0067-02)	30/APR/02	JW	CS
			B	REVISED (ECR-07-015887)	12/DEC/07	DR	JK
			C	REVISED (ECR-11-013205)	28/JUN/11	SJ	HG



- NOTE.
- 1. APPLICABLE ASS'Y CONNECTOR FOR JPT&MQS 81Pos.; P/N: 368290-1
  - 2. TRADE MARK.
  - 3. CAVITY MARK
  - 4. DATE CODE.
  - 5. RECYCLE MARKING.

BLACK	PBT+GF20%	MQS REC HSG TYPE "A" (CHINA ONLY)	9-368293-1
BLACK	PBT+GF20%	MQS REC HSG TYPE "A"	368293-1
COLOR	MATERIAL	DESCRIPTION	P/N

THIS DRAWING IS CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN SJ CHOI CHK JW JUNG APVD HG CHD PRODUCT SPEC APPLICATION SPEC WEIGHT					
DIMENSIONS: MM 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 <XX<10 ± 0.2 10<XX<30 ± 0.25 30<XX ± 0.3 ANGLES ± 3°				NAME <b>MQS REC HOUSING "TYPE A"</b>	
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	
				A3	00779	368293	
				SCALE 2/1		SHEET 1 OF 1	REV C