







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED(FC00-0095-02)	21,JUN,'02	HS	CS
	C	REVISED(ECR-12-010401)	11,JUN,'12	YH	HG
	C1	REVISED PER ECR-23-175897	16MAY2023	RK	JT



- NOTES
- 1. GENERAL TOLERANCE IS ± 0.5
 - ② WARPAGE 1.0 MAX.
THIS WARPAGE WILL BE CORRECTED WITH COVER HOUSING GUIDE WHEN COVER PUTS ON THE HEADER ASSEMBLY.(SEE VIEW 1.)
 - ③ APPLICATION TEST SPEC :
MS210-12-A2[EXT-2](EXCEPT 4.4)



0-368401-X	© 1-368401-X

OBSOLETE	COVER HOUSING	©1-368401-2	PBT-GF15	BLACK
	COVER HOUSING	① 0-368401-2	PBT-GF15	TRAFFIC RED
	COVER HOUSING	0-368401-1	PBT-GF15	BLACK
	DESCRIPTION	Part NO.	MATERIAL	COLOR
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16MAY2023	TE Connectivity	
		CHK -		
DIMENSIONS: mm		APVD -	NAME	
		PRODUCT SPEC -		
 TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm -$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$ FINISH $\pm -$		APPLICATION SPEC -	COVER HSG FOR 40POS	
		WEIGHT -		
MATERIAL SEE NOTE		SIZE A3	CAGE CODE 00779	DRAWING NO C-368401
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	REV C1