






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

creo
 Creo Parametric 2.0
**DO NOT REVISE
 EXCEPT BY CAD**

| | | REVISIONS | | | |
|----|-----|------------------------------|-----------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| C | | REVISED DESIGN ECO-13-018731 | 04DEC2013 | NCL | GOJ |
| CI | | REVISED PER ECN-22-144268 | 13JUN2022 | AP | MT |



PERSPECTIVE VIEWS
 SCALE 1:1


| OBSOLETE | | | | | | | | | | | OBSOLETE | | | | | | | | | | | 2 | COVER CAP | PA6-20%GB+10%GF | VIOLETA / VIOLET |
|----------|---|---|---|---|---|---|---|---|---|---|----------|---|---|---|---|---|---|---|---|---|--|--|-------------|------------------|------------------|
| | | | | | | | | | | | | | | | | | | | | | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | NATURAL | |
| | - | - | - | - | - | - | - | - | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | LARANJA /ORANGE | |
| - | | - | - | - | - | - | - | - | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | ROSA / PINK | |
| - | - | - | | - | - | - | - | - | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | VIOLETA / VIOLET | |
| - | - | - | - | | - | - | - | - | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | CINZA / GRAY | |
| - | - | - | - | - | | - | - | - | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | VERDE / GREEN | |
| - | - | - | - | - | - | | - | - | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | BRANCO / WHITE | |
| - | - | - | - | - | - | - | | - | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | AZUL / BLUE | |
| - | - | - | - | - | - | - | - | | - | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | AMARELO / YELLOW | |
| - | - | - | - | - | - | - | - | - | | - | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | VERMELHO / RED | |
| - | - | - | - | - | - | - | - | - | - | | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | MARROM / BROWN | |
| - | - | - | - | - | - | - | - | - | - | | | - | - | - | - | - | - | - | - | - | | HOUSING, 9 POSN., COMB. JR/STD POWER TIMER | PA6.6+15%GF | PRETO / BLACK | |

| QUANTIDADE POR CONJUNTO / REQUIRED PER ASSY | ITEM | DESCRIPTION | MATERIAL | FINISH |
|---|------|-------------|----------|--------|
| 1--2 1--1 1--0-9-8-7-6-5-4-3-2-1 | | | | |
| 444017 | | | | |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:



0 PLC ±
 1 PLC ±0,3
 2 PLC ±
 3 PLC ±
 4 PLC ±
 ANGLES ±1°
 FINISH -

MATERIAL
 SEE TABLE

DWN H.LIVERARO 04OCT2000
 CHK P.L.FARIA 05OCT2000
 APVD J.A.MARSON 05OCT2000
 PRODUCT SPEC 108-37013
 APPLICATION SPEC -
 WEIGHT -
 Customer Drawing

STE TE Connectivity

NAME -
 HSG., ASSY., 9 POSN.
 COMB. JR., STD POWER TIMER

SIZE A2 CAGE CODE - DRAWING NO C-444017 RESTRICTED TO -
 SCALE 2:1 SHEET 1 OF 1 REV CI