


PROD CODE	LOC	DIS	REV	DATE	APP
4092	DF	50			
REVISIONS			DESCRIPTION	DATE	APP
✓			RLSE PER NPR 88-0267	CT 8-88	95



1. MARKED PER MIL-STD-130.
2. LEAD TO MATE WITH AMP LGH-4 RECEPTACLES WITH 2.00 BARREL DEPTH.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 1. PLC DEC ± .04 2. PLC DEC ± .04 3. PLC DEC ± .04 ANGLES		DR	8-18-88	NAME	
SEE CALLOUTS		APPD	8-21-88	AMP INCORPORATED	
MATERIAL		APPD	8-21-88	MIL-STD-9, Pg. 17105	
FINISH		PRODUCT SPEC	8-21-88	LEAD ASS'Y, LGH-4, SINGLE END	
APPLICATION SPEC		SCALE	1:1	SHIELDED & SILICONE JACKET	
WEIGHT		SIZE	00779	DRAWING NO	
		SCALE	1:1	445514	
		SHEET	1 OF 1	PART NO.	
				445514-1	