



1. THIS RECEPTACLE WILL MATE WITH ANY 36C4, SIZE 5 PLUG IN AMPLIMITE SERIES.
2. MAXIMUM WIRE INSULATION TO BE USED WITH THIS RECEPTACLE IS .068 DIA [1.73].
3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERT ASSEMBLY.
4. CONNECTOR SUPPLIED WITHOUT CONTACTS; SHOWN FOR ILLUSTRATION ONLY.
5. THIS CONNECTOR ACCEPTS SIZE 20 SOCKET CONTACTS.
6. UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL
7. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS. METRIC EQUIVALENTS ARE BASED UPON 1.00 INCH = 25.4 mm.
8. FINISH: CADMIUM PER QQ-P-416.
9. FINISH: ZINC PLATE PER ASTM-B-633 .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+).

$\triangle 9$	5-446711-1
$\triangle 8$	446711-1
NOTES	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 7-14-89	Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: INCHES		CHK A.F.MADI 7-15-89	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.F.MADI 7-15-89	NAME RECEPTACLE ASSEMBLY, AMPLIMITE 36C4, SIZE 5, COAX. MIX, SER 109 W/FLOATING BUSHINGS FOR BLINDMATE
0 PLC ± -		PRODUCT SPEC	APPLICATION SPEC
1 PLC ± -		SIZE	SCALE
2 PLC ± -		WEIGHT	SHEET 1 OF 1
3 PLC ± .005 [0.13]		CAGE CODE	REV C
4 PLC ± -		DRAWING NO	
ANGLES ± -		446711	
FINISH SEE CALLOUTS		CUSTOMER DRAWING	

