

LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
					A	NEW DRAWING		25SEP12	KH	JE

- 2

PHOSPHOR BRONZE
- 3

LCP, UL94V-0
- 4

0.76um MIN GOLD OVER 1.27um MIN NICKEL UNDERPLATE OR GOLD FLASH OVER 0.76um MIN PALLADIUM NICKEL OVER 1.27um MIN NICKEL UNDERPLATE ON CONTACT AREA. 0.76um MIN MATTE TIN OVER 1.27um MIN NICKEL ON COMPLIANT PIN AREA
- 5







CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6

REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES
- 7

APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8

DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9

CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



ROW A: 1-4 ROWS B-K: 1-5	ROW A: 5	5120967-1
PIN LOCATION	PIN LOCATION	PART NUMBER
SIGNAL CONTACT TYPE B QTY: 49	SIGNAL CONTACT TYPE A QTY: 1	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL 25SEP12	TE Connectivity	
DIMENSIONS: mm		CHK FABY JONATHAN 25SEP12	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± - ANGLES ± -		APVD FABY JONATHAN 25SEP12	PRODUCT SPEC	
MATERIAL HOUSING: 3 CONTACTS: 2		FINISH SIGNAL CONTACT: 4	APPLICATION SPEC	
WEIGHT		SIZE A1	CAGE CODE 00779	
CUSTOMER DRAWING		DRAWING NO 5120967	RESTRICTED TO	
SCALE 5:1		SHEET 1	OF 1	
		REV A		