





D



C

B

A



- 1 HOUSING MATERIAL: GLASS-FILLED POLYESTER. COLOR: GRAY.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 4 COMPLIANT PIN REQUIRES 1.57 [.062] MIN THICK PC BOARD, RECOMMENDED PC BOARD HOLES ARE Ø1.151±0.025 [.0453±.0010] DRILLED HOLES WITH 0.02-0.08 [.001-.003] COPPER AND 0.008 [.0003] MIN TIN-LEAD PLATING. FINISHED HOLES AFTER PLATING, Ø0.94-1.09 [.037-.043].
- 5 PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO HOT-STAMPED THIS APPROXIMATE AREA.
- 6 CONTACT POINT.
- 7 HOT-STAMPING ON THIS SIDE.



3	5148359-4
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	28MAR2007	Tyco Electronics Corporation	
		CHK D. BRATINA	28MAR2007	Harriburg, PA 17105-3608	
		APP'D D. BRATINA	28MAR2007	NAME	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RECEPTACLE ASSEMBLY, EUROCARD, TYPE 1/2R, PRESS-FIT, 48 POSITION	
		0 PLC ± -		APPLICATION SPEC	
		1 PLC ± -		SIZE	
		2 PLC ± 0.13[.005]		CAGE CODE	
		3 PLC ± -		DRAWING NO	
		4 PLC ± -		RESTRICTED TO	
		ANGLES ± -		A1 00779 5148359	
MATERIAL		FINISH		CUSTOMER DRAWING	
1 2		SEE TABLE		SCALE 4:1	
				SHEET 1 OF 1	
				REV A	