




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	25AUG2023	ASB	JDB
	B1	DRAWING RE-CREATED IN CREO	27DEC2023	ASB	JDB
	B2	DRAWING CLARIFICATION	02APR2024	ASB	JDB
	B3	REEL CORE DIA CHANGE	25JUL2024	KA	LET

TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 75 PCS



CONSIDER MOUNTING POSITION; PEG RIGHT



1	-	TAPE & REEL	7
1	-	PAD	6
1	-	O-RING	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
5	-	PINS	2
1	-	HOUSING	1
515129-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		





V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)
*=VERSION: WITH CUT-IN, WITHOUT SEAL, WITH O-RING

INSPECTION LEVEL 1: CONTROL CHART REQUIRED
1 PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED


INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
2 PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

3 PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST


INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3



PCB-LAYOUT PROPOSAL



SCALE 2:1
3D VIEW



- DRAWING SPECIFICATION ACCORDING TO 5_3_17-DOC-1810-00294
- COMPLANARITY OF ALL CONTACTS AND CLIPS <=0.1mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S ADRUSH CHK M SZELAG APVD J DE BRUIJN	11JUL2023 13JUL2023 13JUL2023	TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8015	PRODUCT SPEC	108-94887		
MATERIAL	FINISH	WEIGHT	114-94781	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING				DRAWING NO C=515129-E	RESTRICTED TO -
				SCALE 5:1	SHEET 1 OF 1
				REV B3	