

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

H

-

A

ECN EH10 0344 05

09 MAR 05

MG

MG

COLORED
STRIPE

"L" MAX.

OPTIONAL

A


1

2

POS 1

2,5
[0,098]

0,97 [0.038] MAX

SECTION B-B
SCALE 10:15.9 MAX
[.232]2,3
[0,089]3.2 MAX.
[.126]3,0
[0,116]SECTION A-A
SCALE 10:12,8
[0,109]THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
mm (inch)TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

FINISH

2

CONTACT

PHOSPHORBRONZE

TIN OVER NICKEL

1

HOUSING

PBT 20% GF, COLOR GREEN

ITEM NO.

DESCRIPTION

MATERIAL

FINISH

DWN

09 MAR 05

CHK

M. GOSSELINK

APVD

F. FLEIJTENS

PRODUCT SPEC

108-19027

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

-

tyco
ElectronicsTYCO ELECTRONICS NEDERLAND B.V.
's-HERTOGENBOSCH, THE NETHERLANDS

NAME

MINI-MATCH CONNECTOR ASS'Y
3-20 POS 2.5 MM PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=5161500

SCALE 5:1

SHEET 1

OF 1

REV A