




DRAWING MADE IN AMERICAN PROJECTION



ORDER NUMBER	NUMBER OF POSITIONS	'L' MAX.	
		MM.	INCH.
5164897-2	2	5,0	.197
1 OBSOLETE	3	7,5	.295
OBSOLETE	4	10,0	.394
1 OBSOLETE	5	12,5	.492
	6	15,0	.591
	7	17,5	.689
	8	20,0	.787
	9	22,5	.886
1	10	25,0	.984
1	11	27,5	1.083
1	12	30,0	1.181
1	13	32,5	1.280
1	14	35,0	1.378
1	15	37,5	1.476
1	16	40,0	1.575
1	17	42,5	1.673
1	18	45,0	1.772
1	19	47,5	1.870
2-5164897-0	20	50,0	1.969

MATERIAL: HOUSING: P.C., 90% GLASS FILLED.
CONTACT: BRASS
PLATING: TIN OVER NICKEL BARRIER

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



SECTION A-A

SECTION B-B

A2	REVISED AS PER ECN-24-279450	13AUG24	MK	GC
A1	ECO-09-026495	28NOV09	KK	AEG
ltr	rev. rec.	date dwn	apvd	

SEE TABLE.		SEE ABOVE.		SEE ABOVE.	
ORDER NO.		MATERIAL		PLATING	
CUSTOMER COPY FOR REFERENCE ONLY					
DR R. Coolen	DATE 01 MAR 05	©1988 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.		AMP AMP - HOLLAND N.V. 's-Hertogenbosch	
CHK	DATE				
DE	DATE	WIRE-RANGE	INSUL-RANGE	FIRST USED	
APP	DATE	SCALE N.T.S.	SIZE B	NO C-5164897	REV A1
NAME 2-20 POS. MALE HEADER ASS'Y. RIGHT ANGLED FOR MINI MATCH INTERCONNECTION SYSTEM, PITCH: 2,5 mm.					