

WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REV PER ECN-25-311230	13MAR2025	LP	PD


1 TONGUE MATERIAL THICKNESS: .057±.003.



BODY - CU PER ASTM B152
INSERT - BRASS PER ASTM B36



BODY - TIN PLATING PER ASTM B-545
INSERT - .000100 MIN THICK TIN PLATE
PER ASTM B-545



OBSOLETE	1.925	.807	1/2	.515	51982-3
	1.859	.675	3/8	.390	51982-2
	1.859	.675	5/16	.328	51982-1
	1.859	.675	1/4	.265	51982
	"E"	"C"	"B"	"A"	PART NO

1	WIRE TERMINAL	SEE ABOVE TABLE
QTY	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 04APR2008	TE Connectivity		
		CHK JEFF RUTH 04APR2008			
DIMENSIONS: INCHES		APVD JEFF RUTH 04APR2008	NAME		
		PRODUCT SPEC	WIRE TERMINAL COPALUM - STRANDED/SOLID WIRE SIZE #2		
		APPLICATION SPEC			
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO
2		-	A3	00779	C-51982
TOLERANCES UNLESS OTHERWISE SPECIFIED:		FINISH	RESTRICTED TO		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± 5°		3	-		
CUSTOMER DRAWING			SCALE	SHEET	REV
			4:1	1 OF 1	G