





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H2	ECN-22-171534	30AUG2022	RK	JO



1. REFER TO CUSTOMER 582370 SERIES AND CUSTOMER 582380 SERIES FOR HOUSING AND P.C. BOARD REQUIREMENTS
2. .000015 GOLD OVER .000050 NICKEL IN CONTACT AREA. REMAINDER OF CONTACT .000050 NICKEL.
3. .000030 GOLD OVER .000050 NICKEL IN CONTACT AREA. .000050 NICKEL ON REMAINDER OF CONTACT.
4. L-R FEED FOR MINI-APPL.
5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



5	OBSOLETE	MATTE TIN	4	5-530006-5
		MATTE TIN	4	5-530006-2
5	OBSOLETE	2	4	530006-7
		3	4	530006-6
		TIN PLATE	4	530006-5
		2		530006-4
	OBSOLETE	3		530006-3
		TIN PLATE		530006-2
		FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 29MAR01		TE Connectivity				
		CHK M.MILLER 05APR01						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT, 22-18 AWG, DUO-TYNE FLAG WITH TAPERED BEAMS —				
		APVD M.MILLER 05APR01						
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL BERYLLIUM COPPER		FINISH SEE TABLE		SIZE A3	CAGE CODE 00779	DRAWING NO C-530006	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 6:1	SHEET 1 OF 1	REV H2