





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		A1	REVISED PER ECR 10-006882	05APR10	JR	TM



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
12-10 AWG STRANDED	12-10 AWG STRANDED	NOT CERTIFIED

										53015-1			
										PART NO.			
MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN TA BRINKMAN 2-12-93		 Tyco Electronics Corporation Harrisburg, PA 17105-3608					
						CHK DA PATTERSON 2-12-93							
VOLTAGE RATING: N/A		DIMENSIONS: MM[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		APVD JL MECKLEY 2-12-93		NAME TERMINAL, SHORT SPRING SPADE, BUDGET -					
						PRODUCT SPEC -		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED		MATERIAL - 		FINISH - 		WEIGHT -		A2		00779	C-53015	-	
CUSTOMER DRAWING										SCALE 10:1		SHEET 1 OF 1	REV A1