




© - TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECR-24-207629	16MAY2024	SA	DSC

100	LOOSE PC	53949-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150° c		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 10-6-93		 TE Connectivity										
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R. HERSEY 10-6-93		APVD B. BARE 10-6-93							
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 16.77-26.65mm ² [33,100-52,600] STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC NOT AVAILABLE		NAME TERMINAL, RING TONGUE, PVF ² , PLASTI-GRIP, WIRE SIZE: 4 AWG							
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL COPPER PER ASTM B-152 PVF ² , COLOUR: NATURAL		FINISH TIN/LEAD (93-7) PLATE PER ASTM B545		APPLICATION SPEC NOT AVAILABLE		SIZE A3		CAGE CODE 00779		DRAWING NO C-53949		RESTRICTED TO -	
CUSTOMER DRAWING										SCALE NTS		SHEET 1 OF 1		REV F					