



| LOC | DIST | REVISIONS |     |             |      |     |      |
|-----|------|-----------|-----|-------------|------|-----|------|
|     |      | P         | LTR | DESCRIPTION | DATE | DWN | APVD |
| AI  | -    |           |     |             |      |     |      |
|     |      |           |     |             |      |     |      |

| Kontakt<br>Contact       | DGB (mm^2)<br>Wire Range | Drahtcrimp/Wirecrimp |              | Isocrimp     | Iso.-Ø<br>Ins. Range | Betriebsanl.<br>Instr. Sheet |
|--------------------------|--------------------------|----------------------|--------------|--------------|----------------------|------------------------------|
|                          |                          | Hoehe/Height         | Breite/Width | Breite/Width |                      |                              |
| 926893 / 926894 / 926898 | 0.5-1.0                  | 1.26                 | 2.29         | 3.30         | 1.4-2.1              | 411-18125                    |
|                          | 1.5-2.0                  | 1.60                 |              |              | 2.2-2.4              |                              |



|          |             |            |              |                    |     |
|----------|-------------|------------|--------------|--------------------|-----|
| 539652-2 | 1           | 0-539787-3 | locator ass. | Positioniereinheit | A   |
|          | 1           | 1-519151-3 | screw M4x25  | Schraube M4x25     | A   |
|          | 1           | 0-519151-9 | screw M4x10  | Schraube M4x10     | A   |
|          | 1           | 0-519024-2 | hex nut M4   | Mutter M4 DIN 985  | A   |
|          | QTY<br>Stck | PN         | Description  | Benennung          | REV |

|                                                                                                                  |  |                               |                                                            |                    |                          |                    |  |  |
|------------------------------------------------------------------------------------------------------------------|--|-------------------------------|------------------------------------------------------------|--------------------|--------------------------|--------------------|--|--|
| DIMENSIONS:<br>mm-DIN 7168-m                                                                                     |  | DWN<br>M.Weberndorfer 210CT99 | MATERIAL<br>-                                              |                    | FINISH<br>-              |                    |  |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br><br>0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± |  | CHK<br>U.Reuter 220CT99       | <b>AMP</b> tyco Electronics AMP GmbH<br>D - 64625 Bensheim |                    |                          |                    |  |  |
|                                                                                                                  |  | APVD<br>-                     |                                                            |                    |                          |                    |  |  |
|                                                                                                                  |  | PRODUCT SPEC<br>-             | NAME<br>ERGOCRIMP Die Set for<br>Universal/MATE-N-LOK      |                    |                          |                    |  |  |
|                                                                                                                  |  | APPLICATION SPEC<br>-         |                                                            |                    |                          |                    |  |  |
|                                                                                                                  |  | WEIGHT<br>-                   | SIZE<br>A 4                                                | CAGE CODE<br>00779 | DRAWING NO<br>C-539652-2 | RESTRICTED TO<br>- |  |  |
|                                                                                                                  |  | CUSTOMER DRAWING              |                                                            | SCALE<br>2:1       | SHEET<br>1               | OF<br>1            |  |  |
|                                                                                                                  |  |                               |                                                            | REV<br>A           |                          |                    |  |  |