





① MATERIAL: HOUSING — PBT POLYESTER,
BLACK.
TERMINAL $-0.33[.013]$ THICK PHOS-BRONZE PLATED WITH
 $1.27\mu\text{m}[.000050]$ MINIMUM THICK HARD GOLD IN
LOCALIZED GOLD PLATE AREA AND $3.81\mu\text{m}$
 $[.000150]$ MINIMUM THICK MATTE TIN IN SOLDER
AREA OVER $1.27\mu\text{m}[.000050]$ MINIMUM THICK
NICKEL UNDERPLATE.


② CAVITY CONFORMS TO FCC RULES AND
REGULATIONS PART 68, SUBPART F.


3. THIS DRAWING RESTRICTED TO AMP ITALY.

④ CAUTION: CATEGORY 5 JACK SOLDER TAIL
POSITIONS DO NOT FOLLOW SAME NUMBER
SEQUENCE AS THAT OF TRADITIONAL JACKS.



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SEE APPLICATION SPECIFICATION



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07JUN2005 L. VARELA - DOCK5 CHK 07JUN2005 J. WESTMAN APVD 07JUN2005 S. FLICKINGER		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± ± - ANGLES		NAME MODULAR JACK ASSEMBLY;8 POSN, R/A ,LOW PROFILE,WITH RIGHT PANEL STOP,CAT 5e	
		PRODUCT SPEC 108-1163 APPLICATION SPEC 114-2048		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-5569807 -	
MATERIAL 		FINISH 		WEIGHT 0.000000 RESTRICTED CUSTOMER	
				SCALE 4:1 SHEET 1 of 1 REV A1	