

SPECIFICATION CONTROL DRAWING

SCD

55A0814

Title WIRE, RADIATION-CROSSLINKED, MODIFIED ETFE-INSULATED,
NORMAL WEIGHT, GENERAL PURPOSE, 600 VOLT

Date 1-12-17

Revision N

This specification sheet forms a part of the latest issue of Raychem Specification 55A.




TABLE I. CONSTRUCTION DETAILS

PART NUMBER <u>1/</u>	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	DIAMETER OF STRANDED CONDUCTOR (inch)		FINISHED WIRE		
			MINIMUM	MAXIMUM	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (inch)	MAXIMUM WEIGHT (lbs/1000 ft.)
55A0814-26-*	26	19 x 38	.018	.020	44.8	.040 ± .002	1.70
55A0814-24-*	24	19 x 36	.023	.024	28.4	.045 ± .002	2.30
55A0814-22-*	22	19 x 34	.029	.031	17.5	.050 ± .002	3.30
55A0814-20-*	20	19 x 32	.037	.039	10.7	.058 ± .002	4.80
55A0814-18-*	18	19 x 30	.046	.050	6.8	.070 ± .003	7.50

TABLE II. PERFORMANCE DETAILS

PART NUMBER <u>1/</u>	MANDREL DIAMETER (inch) (± 3%)		WEIGHT (lb) (± 3%)	
	LIFE CYCLE, IMMERSION, AND ACCELERATED AGING	COLD BEND	LIFE CYCLE, IMMERSION, AND ACCELERATED AGING	COLD BEND
55A0814-26-*	.375	1.00	.500	3.00
55A0814-24-*	.500	1.00	.750	3.00
55A0814-22-*	.500	1.00	1.00	3.00
55A0814-20-*	.500	1.00	1.50	4.00
55A0814-18-*	.750	1.50	2.00	4.00

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.





WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

ACCELERATED AGING (CROSSLINKING PROOF): 300 ± 3°C for 7 hours

BLOCKING: 230 ± 3°C for 24 hours

COLOR: White preferred

CONCENTRICITY: 70% (minimum)

FLAMMABILITY: Procedure 1, 3 seconds (maximum), 3 inches (maximum);

no flaming of facial tissue

HUMIDITY RESISTANCE: Insulation Resistance, 5000 megohms for 1000 ft. (minimum)

IDENTIFICATION, COLOR STRIPING, AND BAND DURABILITY:

125 cycles (250 strokes) (minimum), 500 g weight

IMMERSION: Diameter increase 5% (maximum); no cracking, no dielectric breakdown

INSULATION ELONGATION AND TENSILE STRENGTH:

Elongation,

125% (minimum) for primary insulation

75% (minimum) for total insulation (primary insulation & jacket)

Tensile Strength,

5000 lbf/in² (minimum) for primary insulation

5000 lbf/in² (minimum) for total insulation (primary insulation & jacket)

INSULATION FLAWS:

Primary Insulation,

Spark Test, 1.5 kV (rms) at 60 Hz; 4.2 kV (rms) at 3 kHz

Impulse Dielectric Test, 6.0 kV (peak)

Finished Wire,

Spark Test, 5.7 kV (rms) at 3 kHz

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION RESISTANCE: 5000 megohms for 1000 ft. (minimum)

INSULATION THICKNESS:

0.003 in. (minimum) for primary insulation

0.004 in. (minimum) for outer jacket

0.009 in. (minimum) for total insulation

LIFE CYCLE: 230 ± 3°C for 500 hours

LOW TEMPERATURE-COLD BEND: -65 ± 3°C for 4 hours

SHRINKAGE: 230 ± 3°C for 6 hours, 0.125 in. (maximum) in 12 inches

SMOKE TEST: 250 ± 5°C, no visible smoke

SOLDERABILITY: Per MIL-STD-202, Method 208, except without steam aging

SURFACE RESISTANCE: 500 megohms-in. (minimum), both readings

THERMAL SHOCK RESISTANCE: 200 ± 3°C, 0.060 in. (maximum)

VOLTAGE WITHSTAND (Post Environmental): 2500 volts (rms), 60 Hz

WICKING: 2.25 in. (maximum)

WRAP TEST: 313 ± 3°C for 2 hours

1/ PART NUMBER:

The "*" in the part numbers in Tables I and II shall be replaced by a color code designator.

Example: AWG 22, white: 55A0814-22-9

AWG 22, white with a black stripe: 55A0814-22-90