

**TWO CONDUCTOR CABLE, RADIATION CROSSLINKED, MODIFIED FLUOROPOLYMER INSULATED,
TINNED COPPER CONDUCTOR, LIGHTWEIGHT, 150°C, 600 VOLT**

The complete requirements for procuring the wire described herein shall consist of this document.

Component wire -
55A0111



Part Number	Conductor Size (AWG)	Outside Diameter (mm)		Maximum Weight (kg/km)
		Nom.	Max.	
55CD0264-28-*/*	28	1.37	1.47	2.99
55CD0264-26-*/*	26	1.63	1.73	4.74

COLOUR CODE:

The '*' in the part number shall be replaced by a standard colour code designator in accordance with Mil Std 681.
eg: 55CD0264-26-2/6, size 26, cores red, blue.

**PERFORMANCE
REQUIREMENTS:**

Special Lay Length 6.00 ±1.00 mm Left Hand.
Except as specified in this document, this product shall meet all the requirements of the issue in effect of 55A0121 SCD.

DESIGN	PROD. MAN.	TECHNICAL	MANUFACTURE
<i>[Signature]</i> 18/11/02	<i>[Signature]</i> 21/11/02	<i>[Signature]</i> 21/11/02	<i>[Signature]</i> 21/11/02 P.R. BL.

[Signature]
21/11/02