


Specification Control Drawing

TWO CONDUCTOR CABLE, MODIFIED FLUOROPOLYMER INSULATED,  
450 VOLT, 200°C, LIGHTWEIGHT

The complete requirements for procuring the wire described herein shall consist of this document.



Part Description	Wire Size	Outside Diameter (mm)		Weight (kg/km)	
		Target	Max	Target	Max.
55M0424-30-*/*	30	1.03	1.10	1.42	1.77
55M0424-28-*/*	28	1.17	1.24	1.90	2.42
55M0424-26-*/*	26	1.37	1.45	3.04	3.66
55M0424-24-*/*	24	1.63	1.70	4.66	5.44

COLOUR CODE: The '\*' in the part number shall be replaced by a standard colour code designator in accordance with Mil Std 681.

e.g. 55M0424-24-0/9, size 24, cores black, white.

PERFORMANCE REQUIREMENTS: Component wires must conform to 55M0414 SCD.  
Insulation flaws  
100% Spark Test :- 8kV Impulse.

APPROVAL: Electronic sign off - no signatures will appear.

Tyco Electronics UK Ltd  
Faraday Road  
Dorcan  
SWINDON  
SN3 5HH  
UK

Registration Number:  
550926 London, England

This drawing and the information set forth hereon are the property of Tyco Electronics UK Ltd, and are to be held in trust and confidence. Publication, duplication, disclosure or use for any purpose not expressly authorised in writing by Tyco Electronics UK Ltd is prohibited.

This specification sheet takes precedence over documents referenced herein. As Tyco Electronics UK Ltd. reserve the right to make changes in construction without notice please contact Tyco Electronics UK Ltd to ensure that this document is the latest issue

Tel: 0800 267666  
Fax: 01793 572516

Website: [www.tycoelectronics.com](http://www.tycoelectronics.com)  
Email: [picuk@tycoelectronics.com](mailto:picuk@tycoelectronics.com)