SPECIFICATION CONTROL DRAWING								55PC0121	
Title	TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, GENERAL PURPOSE, 600 VOLT Data							20-17	Revision E
	This spec	ification sheet forms	s a part of the la	atest issue of	Raychem Spec	ification 55P	С.		
	COMPONENT WIRES - 55PC0111								
					\checkmark				
					\rightarrow				
								_	
		CABLE CONSTRUCTION DETAILS							
	PART NUMBER	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)			WEIGHT (lbs/1000 ft.)			
	<u>1</u> /		LOWER	WER TARGET UPPER		TARGET	UPPER		
		, ,	SPEC LIMIT	VALUE	SPEC LIMIT	VALUE	SPEC LIMIT		
	55PC0121-30-*	30	.044	.047	.050	1.21	1.29		
	55PC0121-28-*	28	.050	.053	.056	1.69	1.80		
	55PC0121-26-* 55PC0121-24-*	26 24	.058	.061 .071	.064	2.49	2.67		
	55PC0121-24-	24	.068 .080	.071	.074	3.66 5.44	3.85 5.67		
	55PC0121-22-	22	.080	.083	.000	8.32	8.57		
	55PC0121-18-*	18	.115	.033	.101	12.69	13.14		
	55PC0121-16-*	16	.130	.133	.121	16.21	16.72		
	55PC0121-14-*	14	.158	.162	.166	25.08	25.74		
	55PC0121-12-*	12	.196	.200	.204	38.80	39.68		
							•	4	
		CABLE RATI	INGS AND ADE	DITIONAL RE	QUIREMENTS				
	TEMPERATURE RATING: 150°C Maximum continuous conductor temp	oroturo		<u>1</u> / PART N	UMBER: " in the part nu	mhoro obovo	chall be replac	ad by color oc	do
	VOLTAGE RATING: 600 volts (rms) at				nators with a sla				Je
	INSULATION FLAWS: Spark Test, 3.0 kV (rms)			Exam	ple: AWG 22, 55PC012		component wir	es:	
	Impulse Dielectric Test, 6.0 kV (peak)				551 6012	1-22-2/0			
	Users should evaluate Tyco Electronics also reserves the right to ma	· · · · · · · ·						tification to Buye	er.
	1/ COLORS AND COLOR CODE DESIGNATORS AN ALTERNATIVE COLOR CODE MAY REP AND SUFFIXES MAY BE ADDED TO THE P	ACE MIL-STD-681 COLC	OR CODE DESIGNA	TORS. (EXAMPL	E: "901/902" MAY	' BE REPLACED	BY "Axxx".) OTHE	RCODES	
	Raychem, TE Connectivity, TE connectivity (logo), and TE (logo are trademarks.								Raychem Wire & Cable
Page 1 of 1	DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL.							TE	501 Oakside Avenue Redwood City, CA 94063-3800
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.							connectivity	Phone: 1-800-522-6752 Fax: 1-650-361-6297