








LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DY	-		0	NPR FP00-0340-04	5JAN05	LWY	LSF

NOTES:

- 1 HOUSING: THERMOPLASTIC, UL 94V-0 RATED, GRAY
- 2 CONTACT & SHIELD: COPPER ALLOY
- 3 CONTACT: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 1.52 [.060] MIN FROM MATING END, 3.05um [.000120] MIN MATTE-TIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL, ENTIRE CONTACT.
- 4 SHIELD: PRE-TIN PLATED



DETAIL E
SCALE 50:1

P/N: 5750725-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ANY DISCREPANCY BETWEEN THIS DRAWING AND THE CONTROLLING DOCUMENT ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE	05JAN2005	tyco Electronics	Tyco Electronics Singapore Pte. Ltd.		
DIMENSIONS: mm[INCHES]		CHK WYLEE	APVD SE LEONG		NAME RECEPTACLE ASSY, W/ HOLD DOWN, SPECIAL, 7 POS, RIGHT ANGLE, MINIATURE CIRCULAR DIN		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC					
0 PLC ±.013		108-1225					
1 PLC ±.013		APPLICATION SPEC					
2 PLC ±.013		114-40031					
3 PLC ±.013		WEIGHT					
4 PLC ±.013		FINISH					
5 PLC ±.013		CUSTOMER DRAWING					
6 PLC ±.013		SCALE 5:1					
7 PLC ±.013		SHEET					
8 PLC ±.013		OF 1					
9 PLC ±.013		REV 0					