


REV	DATE	DESCRIPTION	BY	APP'D
A	20AUG96	RELEASE PER NPR PD 96-0054	LMH	RS
A1	07DEC09	REVISED PER ECO-09-022178	KK	AEG



- CABLE CERTIFIED TO: -UL CABLE STYLE: 2651
CSA: CSA AWM IA 105°C 300V FT1
- CABLE PHYSICAL SPECIFICATIONS:
 - TEMPERATURE RATING: -20°C TO +105°C
 - FLAMMABILITY: -UL: VWI
 - INSULATION: GRAY FLAME RETARDANT FLEXIBLE PVC
 - CONDUCTORS: 26 AWG 7/34 STRANDED TINNED COPPER
- ELECTRICAL REQUIREMENTS:
 - VOLTAGE: 300 VOLTS
- EDGE MARK ON CONDUCTOR #1
- LENGTH PER REEL: 250 FT. REEL MAY CONTAIN SEPARATE LENGTHS. 20 FT. MIN PER LENGTH. TWO LENGTHS MAX PER REEL.
- LENGTH PER REEL: 100 FT. REEL MAY CONTAIN SEPARATE LENGTHS. 20 FT. MIN PER LENGTH. TWO LENGTHS MAX PER REEL.
- CABLE SURFACE PRINTED PER UL & CSA REQUIREMENTS.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

REEL LENGTH	B REF	NO. OF CNDTS	PART NUMBER
2.800	2.700±.010	28	5-57744-8
2.700	2.600±.010	27	5-57744-7
2.600	2.500±.010	26	5-57744-6
2.500	2.400±.010	25	5-57744-5
2.400	2.300±.010	24	5-57744-4
2.300	2.200±.010	23	5-57744-3
2.200	2.100±.010	22	5-57744-2
2.100	2.000±.009	21	5-57744-1
2.000	1.900±.009	20	5-57744-0
1.900	1.800±.009	19	4-57744-9
1.800	1.700±.009	18	4-57744-8
1.700	1.600±.009	17	4-57744-7
1.600	1.500±.008	16	4-57744-6
1.500	1.400±.008	15	4-57744-5
1.400	1.300±.008	14	4-57744-4
1.300	1.200±.008	13	4-57744-3
1.200	1.100±.008	12	4-57744-2
1.100	1.000±.007	11	4-57744-1
1.000	.900±.007	10	4-57744-0
.900	.800±.007	9	3-57744-9
.800	.700±.007	8	3-57744-8
.700	.600±.007	7	3-57744-7
.600	.500±.006	6	3-57744-6
.500	.400±.006	5	3-57744-5
.400	.300±.005	4	3-57744-4
.300	.200±.005	3	3-57744-3
.200	.100±.005	2	3-57744-2
2.800	2.700±.010	28	2-57744-8
2.700	2.600±.010	27	2-57744-7
2.600	2.500±.010	26	2-57744-6
2.500	2.400±.010	25	2-57744-5
2.400	2.300±.010	24	2-57744-4
2.300	2.200±.010	23	2-57744-3
2.200	2.100±.010	22	2-57744-2
2.100	2.000±.009	21	2-57744-1
2.000	1.900±.009	20	2-57744-0
1.900	1.800±.009	19	1-57744-9
1.800	1.700±.009	18	1-57744-8
1.700	1.600±.009	17	1-57744-7
1.600	1.500±.008	16	1-57744-6
1.500	1.400±.008	15	1-57744-5
1.400	1.300±.008	14	1-57744-4
1.300	1.200±.008	13	1-57744-3
1.200	1.100±.008	12	1-57744-2
1.100	1.000±.007	11	1-57744-1
1.000	.900±.007	10	1-57744-0
.900	.800±.007	9	57744-9
.800	.700±.007	8	57744-8
.700	.600±.007	7	57744-7
.600	.500±.006	6	57744-6
.500	.400±.006	5	57744-5
.400	.300±.005	4	57744-4
.300	.200±.005	3	57744-3
.200	.100±.005	2	57744-2

DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 1. PLC DEC ±.1 2. PLC DEC ±.02 3. PLC DEC ±.005 4. PLC DEC ±.0005 ANGLES ±		M.B. BOLES R. SPEER M. RUBERA 04DEC95 04DEC95 04DEC95		AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL: - FINISH: -		WEIGHT: -		SIZE: A1 CASE CODE: 00779 DRAWING NO: C-57744		SCALE: 20:1 SHEET: 1 OF 1 REV: A1	