

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H3	REVISED PER ECN-22-171534	30AUG2022	RK	JO

- 1

BRIGHT TIN-LEAD.
- 2


.000030 THICK NICKEL.
- 3

GOLD FLASH OVER .000030 NICKEL.
- 4


PLAIN.
- 5

MATTE TIN.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SUPSD BY 583857-7	5	5-583857-5
	4	583857-8
	3	583857-7
	2	583857-6
	1	583857-5
OBSOLETE	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. STAUB BG		02AUG93		 TE Connectivity					
		CHK H ROSE		01MAR94							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD H ROSE		01MAR94		NAME CONTACT TWIN LEAF PRE-CRIMPED —			
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —							
		MATERIAL PHOS BRONZE		FINISH SEE TABLE		APPLICATION SPEC —					
		WEIGHT —		SIZE A2		CAGE CODE 00779		DRAWING NO C=583857		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV H3			