

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
FT	0	B2	OBSOLETING PART NUMBERS 15 POSITION AND ABOVE	27MAR2015	CR PS	

MATERIAL:
 HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.
 TERMINALS: BRIGHT TIN PLATED, COPPER ALLOY.
 SCREWS: 6-32, STEEL, ZINC PLATED W/ CLEAR CHROMATE.


ELECTRICAL:
 UL CLASS C: 20A, 150V.
 UL CLASS D: 10A, 300V.
 CSA TYPE B: 20A, 300V.
 CSA TYPE C: 20A, 300V.
 CSA TYPE D: 10A, 300V.
 CSA TYPE E: 20A, 300V.
 WIRE RANGE: 12-22 AWG.

MECHANICAL:
 OPERATING TEMP.: -40° TO +105°C.
 RECOMMENDED TIGHTENING TORQUE: 7 IN-LBS.

- ① SCREWS BOTTOMED.
- ② PRELIMINARY PART NUMBER.
- ③ OBSOLETE PARTS.



REV	DESCRIPTION	DATE	DWN	APVD	COMMENTS	DIM B	DIM A	NO. OF POS.	CATALOG NUMBER	TE PART NO.
③	OBSOLETE	SEE NOTE	9.425	9.815	28	4DB-P208-28			2-1546460-8	
③	OBSOLETE	SEE NOTE	9.100	9.490	27	4DB-P208-27			2-1546460-7	
③	OBSOLETE	SEE NOTE	8.775	9.165	26	4DB-P208-26			2-1546460-6	
③	OBSOLETE	SEE NOTE	8.450	8.840	25	4DB-P208-25			2-1546460-5	
③	OBSOLETE	SEE NOTE	8.125	8.515	24	4DB-P208-24			2-1546460-4	
③	OBSOLETE	SEE NOTE	7.800	8.190	23	4DB-P208-23			2-1546460-3	
①③	OBSOLETE	SEE NOTE	7.475	7.865	22	4DB-P208-22-092			2-796988-0	
③	OBSOLETE	SEE NOTE	7.150	7.865	22	4DB-P208-22			6-1437667-2	
③	OBSOLETE	SEE NOTE	6.825	7.540	21	4DB-P208-21			2-1546460-1	
③	OBSOLETE	SEE NOTE	6.825	7.215	20	4DB-P208-20			2-1546460-0	
③	OBSOLETE	SEE NOTE	6.500	6.890	19	4DB-P208-19			1-1546460-9	
③	OBSOLETE	SEE NOTE	6.175	6.565	18	4DB-P208-18			1-1546460-8	
③	OBSOLETE	SEE NOTE	5.850	6.240	17	4DB-P208-17			1-1546460-7	
③	OBSOLETE	SEE NOTE	5.525	5.915	16	4DB-P208-16			1-1546460-6	
③	OBSOLETE	SEE NOTE	5.200	5.590	15	4DB-P208-15			1-1546460-5	
			4.875	5.265	14	4DB-P208-14			1-1546460-4	
			4.550	4.940	13	4DB-P208-13			1-1546460-3	
			4.225	4.615	12	4DB-P208-12			1-1546460-2	
			3.900	4.290	11	4DB-P208-11			1-1546460-1	
			3.575	3.965	10	4DB-P208-10			1-1546460-0	
			3.250	3.640	9	4DB-P208-09			1546460-9	
			2.925	3.315	8	4DB-P208-08			796658-5	
			2.600	2.990	7	4DB-P208-07			796658-5	
			2.275	2.665	6	4DB-P208-06			796658-4	
			1.950	2.340	5	4DB-P208-05			1546460-5	
			1.625	2.015	4	4DB-P208-04			6-1437667-1	
			1.300	1.690	3	4DB-P208-03			1546460-3	
			.975	1.365	2	4DB-P208-02			6-1437667-0	



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 10/3/03	TE Connectivity			
DIMENSIONS: INCHES		CHK S YODER 10/3/03				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S YODER 10/3/03	NAME			
0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± .005 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC	4DB SERIES P208 STYLE			
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH		WEIGHT	A3	00779	C-6-1437667-0	-
CUSTOMER DRAWING			SCALE	SHEET	REV	
			NTS	1 OF 1	B2	