






| P | LTR | DESCRIPTION  | DATE      | DWN | APVD |
|---|-----|--------------|-----------|-----|------|
|   | A   | NEW RELEASED | 23JUL2020 | GK  | OD   |
|   |     |              |           |     |      |
|   |     |              |           |     |      |
|   |     |              |           |     |      |

NOTES:


- 1

MATERIAL: COPPER-ZINC LEAD ALLOY  
FINISH: f1Cu+Ni2Au0.2µm PASSIVATED
- 2

PLATING THICKNESS MEASUREMENT POINT



|                            |                |                 |                 |
|----------------------------|----------------|-----------------|-----------------|
| 0.14 - 0.5 mm <sup>2</sup> | I              | 60.205.11       | 60-0205-011-000 |
| CRIMPING RANGE             | WEIGHT (g) REF | INTERCONTEC P/N | TE P/N          |

|                                                                                                   |  |                                                                                                 |                                                                                                       |                               |
|---------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|-------------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                            |  | DWN 23JUL2020<br>GOPALAKRISHNA HV                                                               |  TE Connectivity |                               |
|                                                                                                   |  | CHK 23JUL2020<br>ONDREJ DUSAN                                                                   |                                                                                                       |                               |
| DIMENSIONS:<br>mm                                                                                 |  | APVD 23JUL2020<br>ONDREJ DUSAN                                                                  | NAME<br>CONTACT SOCKET 0.6 MM, CRIMPING<br>RANGE 0.14 - 0.5 MM2, SLOTTED                              |                               |
|              |  | PRODUCT SPEC<br>-                                                                               |                                                                                                       |                               |
|                                                                                                   |  | APPLICATION SPEC<br>-                                                                           | SIZE<br>A3                                                                                            |                               |
| MATERIAL<br> |  | WEIGHT<br>SEE TABLE                                                                             | CAGE CODE<br>00779                                                                                    | DRAWING NO<br>60-0205-011-000 |
|                                                                                                   |  | FINISH<br> | RESTRICTED TO<br>-                                                                                    | SCALE<br>10:1                 |
|                                                                                                   |  |                                                                                                 | SHEET<br>1 OF 1                                                                                       | REV<br>A                      |
|                                                                                                   |  |                                                                                                 |                                                                                                       |                               |