

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASED	14MAY2024	NK	OD

NOTES:
I PLATING THICKNESS MEASUREMENT POINT









TABLE 2

0.35 - 2.5 mm ²	2	60.254.11	60-0254-011-P00
CRIMPING RANGE	WEIGHT (g) REF	INTERCONTEC P/N	TE P/N

TABLE 1

LIST OF PARTS				
POS	PIECE	COMPONENT COMPOSED OF	MATERIAL	SURFACE
1	1	CONTACT SOCKET 2 MM	COPPER-ZINC LEAD ALLOY	fl.Cu+Ni2Au0.2µm PASSIVATED
2	1	CONTACT TENSION SPRING	COPPER (2.1247.54 (CuBe2 F520))	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 14MAY2024	 TE Connectivity		
DIMENSIONS: mm		CHK ONDREJ DUSAN 14MAY2024			
		APVD ONDREJ DUSAN 14MAY2024	NAME CONTACT SOCKET 2 MM, CRIMPING RANGE 0.35 - 2.5 MM2, WITH TENSION SPRING SLOTTED		
		PRODUCT SPEC -	SIZE A3		
MATERIAL SEE TABLE 1		APPLICATION SPEC -	CAGE CODE 00779		
FINISH SEE TABLE 1		WEIGHT SEE TABLE 2	DRAWING NO 60-0254-011-P00		
		CUSTOMER DRAWING	RESTRICTED TO -		
			SCALE 5:1		
			SHEET 1 OF 1		
			REV A		