


THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
CM	00	H2	REVISED PER ECR-21-121349	10JAN2022	GK	SCD

1. PACKAGED IN HEAT SEALED 3 MIL POLYBAG.
2. MIL NO. MS3367-3.

△ SPECIAL MARKINGS: THREE TOTAL
 1ST MARKING: BLACK, 4" FROM POINTED END.
 2ND MARKING: BLACK, 6" FROM POINTED END.
 3RD MARKING: BLACK, 9.5" FROM POINTED END.

UNIT OF MEASURE	A	B	C	D	E	L	MAX BUNDLE DIAMETER	MIN TENSILE STRENGTH
INCHES	.375	.496	.303	.325	.078	15.36	4.0	120 LBS
MM	9.53	12.6	7.7	8.26	1.98	390.	101.6	54.43 KG



OBSOLETE	-	3-604773-7	PHOSPHOR YELLOW 500	△
OBSOLETE	-	3-604773-8	PHOSPHOR YELLOW 500	
	-	3-604773-0	BLACK 500	
	-	1-604773-0	BLACK 100	
OBSOLETE	-	3-604773-9	NATURAL 500	
	-	1-604773-9	NATURAL 100	
DWG SIZE		PART NO.	DESCRIPTION	ITEM NO.

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. BY TYCO ELECTRONICS CORPORATION.

DIMENSIONS: MM	DWN	L. McEACHIN	26JUL00	MATERIAL	NYLON 6/6	FINISH	-
	CHK	S. RIDGILL	25-JUL-2000				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	S. RIDGILL	25-JUL-2000				
0 PLC ± -	PRODUCT SPEC	-		NAME			
1 PLC ± -	APPLICATION SPEC	-		HEAVY DUTY CABLE TIE, 15 INCH			
2 PLC ± -	WEIGHT	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ± -				A4	00779	C=604773	-
4 PLC ± -				CUSTOMER DRAWING			
ANGLES ± -				SCALE	1:1	SHEET	1 OF 1
						REV	H2

AMP 1469-35 REV 31MAR2000