




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASED	22JUL2020	GK	OD




NOTES:

- | | |
|---|--|
| 1 | MATERIAL: COPPER-ZINC LEAD ALLOY
FINISH: f1Cu+Ni2Au0.2μm PASSIVATED |
| 2 | PLATING THICKNESS MEASUREMENT POINT |



0.24-1.0 mm ²	I	61.072.11	61-0072-011-000
CRIMPING RANGE	WEIGHT (g) REF	INTERCONTEC P/N	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22 JUL 2020 GOPALAKRISHNA HV CHK 22 JUL 2020 ONDREJ DUSAN APVD 22 JUL 2020 ONDREJ DUSAN		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT PIN 1.5 MM, CRIMPING RANGE 0.24 - 1.0 MM2	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±0° 30'			
MATERIAL 		FINISH 			
WEIGHT SEE TABLE		SIZE A3			
CUSTOMER DRAWING		CAGE CODE 00779		DRAWING NO C-61-0072-011-000	
RESTRICTED TO -		SCALE 5:1		SHEET 1 OF 1	
REV A					