




- NOTES:
- 1 ATTENUATION $\leq 0,5$ dB(MT-RJ) AND $\leq 0,3$ dB(ST), MEASURED AT 1300nm ACC. TO IEC 61300-3-4 EQUILIBRIUM MODE CONDITION
- 2 INDIVIDUAL LENGTH DIFFERENCE ON SC SIDE ≤ 50 mm
- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- 4 DAT LABEL INFO:
— UNIQUE SERIAL NUMBER
— TYCO LOGO PN
— MANUFACTURING LOCN.
- 5 CROSS OVER AS PER BELOW TABLE

FIBRE COLOR	LEFT CONN.	RIGHT CONN.
WHITE	ST RED	MT-RJ B
GREEN	ST BLACK	MT-RJ A

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-6206620-Y	XY,0
8-6206620-4	0,40 -0,05/+0
9-6206620-1	1,5
9-6206620-2	2,5

1	—	DAT-85 LABEL	15
1	—	DUST COVER, MT-RJ	14
1	—	HOUSING, CONN, MT-RJ,BLACK	13
1	—	MT/RJ FERRULE, THERMOPLAST,MM	12
1	—	PIN KEEPER, 3.8MM	11
1	—	SPRING, MT-RJ, 3.8 DESIGN	10
1	—	MT-RJ, SPRING PUSH, UNIVERSAL	9
1	—	CRIMP EYELET, MT-RJ	8
1	—	MT-RJ BOOT, TWIN ZIP BEIGE	7
2	—	PROTECTIVE COVER, 2.5MM, BLACK	6
2	—	ST CERAMIC, OVERMOLDED	5
2	—	FOAC CRIMP EYELET 2.0	4
1	—	FOAC BOOT 2.0 BLACK SC/FC	3
1	—	FOAC BOOT 2.0 BLACK SC/FC	2
L	—	FOCAB 1.8T MZ 50/125 OM2 LSZH, ORANGE	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN

GIRIYAPPA. M

26 AUG 05

CHK

DIWAKAR BELAVADI

26 AUG 05

APVD

DIWAKAR BELAVADI

26 AUG 05

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

Tyco Electronics Corporation
FOBU, Bangalore, India

NAME

FOMM 50 1,8mm MZ DPX ST-MTRJ

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=6206620

—

SCALE

NTS

SHEET

1

OF

1

REV

A

AMP 1471-9 REV 31MAR2000