


LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DMN	APVD
0		REL 94-3180-024-1 THRU -B	8-20-96	LM	JH
A		REV PER 0820-1055-96	11-5-96	LM	JH

- ① CABLE, JACKETED WITH BRAID, 30 AWG, 18 SHIELDED TWISTED PAIR, 100 OHMS DIFF.
- 2. SEE SHT #2 FOR WIRING SCHEMATIC
- ③ SHIELD ON PAIRS 8,9,17 & 18 ARE NOT TERMINATED.
- ④ LABEL PRINTED AS SHOWN:
AMP PART NO
DATE CODE
COUNTRY OF ORIGIN



CONNECTOR P1

CONNECTOR P2


5000±50 [196.85±1.97]	-	-	-	-	621072-9
2438.40±38.10 [96.00±1.50]	-	-	-	-	621072-8
1524.00±25.4 [60.00±1.00]	-	-	-	-	621072-7
610±10 [24.02±.394]	-	-	-	-	621072-6
457.20±25.4 [18.00±1.00]	-	-	-	-	621072-5
4000±35 [157.48±1.38]	-	-	-	-	621072-4
2000±25 [78.74±.98]	-	-	-	-	621072-3
1000±25 [39.37±.98]	-	-	-	-	621072-2
3000±25 [118.11±.98]	-	-	-	-	621072-1
L	④ LABEL QTY=1	③ CABLE QTY=AR	① KIT, .8MM BACKSHELL QTY=2	② KIT .8MM, 50 POSN CHAMP QTY=2	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm (INCHES)	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DMN L. MORNINGSTAR 9-20-96	AMP Incorporated Harrisburg, PA 17105-3508
0 PLC ±.01	1 PLC ±.02	CHK J. HACKMAN 9-20-96	NAME LEAD ASSY, .8MM CHAMP™ , 50 POSN
2 PLC ±.03	3 PLC ±.04	AMPD J. HACKMAN 9-20-96	
4 PLC ±.05	ANGLES ±.5°	PRODUCT SPEC	SIZE A1
MATERIAL	FINISH	APPLICATION SPEC	CAGE CODE 00779
		WEIGHT	DRAWING NO 621072
		CUSTOMER DRAWING	SCALE 2:1
			SHEET 1 OF 2
			REV A

LOC		DIST		REVISIONS			
P	CF	LTR	DESCRIPTION	DATE	OWN	APVD	
-	39	-	SEE SHT#1	-	-	-	

WIRING SCHEMATIC



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. MORNINGSTAR 9-20-96	AMP Incorporated Harrisburg, PA 17105-3508	
DIMENSIONS in (INCHES)		OK J. HACKMAN 9-20-96	NAME LEAD ASSY, .8MM CHAMP™ , 50 POSN	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		AMPD J. HACKMAN 9-20-96	DRAWING NO A1 00779 C-621072	
0 PLC ±.010		PRODUCT SPEC		
1 PLC ±.010		APPLICATION SPEC		
2 PLC ±.010		WEIGHT		
3 PLC ±.010		CUSTOMER DRAWING		
4 PLC ±.010		SCALE 2:1		
ANGLES ±.010		SHEET 2 OF 2		
FINISH		REV A		