


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CF	39	B	ECR-06-026101	28NOV06	JAK JE



DB25 M	DB25 M	DB25 M	DB25 M
P1	P2	P1	P2
1	1	14	14
2	2	15	15
3	3	16	16
4	4	17	17
5	5	18	18
6	6	19	19
7	7	20	20
8	8	21	21
9	9	22	22
10	10	23	23
11	11	24	24
12	12	25	25
13	13	SHELL	SHELL

PART NO.	"L"(IN)	TOL.(IN)	LABEL XX'
621797-1	36.00	+1.00/-0.50	3
621797-2	72.00	+6.00/-2.00	6
621797-3	120.00	+6.00/-2.00	10
621797-4	1200.00	+12.00/-6.00	100
621797-5	180.00	+6.00/-2.00	15
621797-6	240.00	+6.00/-2.00	20
621797-7	300.00	+6.00/-2.00	25
621797-8	420.00	+12.00/-6.00	35
621797-9	600.00	+12.00/-6.00	50
1-621797-0	900.00	+12.00/-6.00	75

OBSOLETE

- 1. 28 AWG, STRANDED TINNED COPPER, 25 COND WITH DRAIN, 100% ALUMINUM MYLAR FOIL PLUS 10% NOMINAL OVERLAP, BEIGE.
- 2. PACKAGED IN PRINTED ZIPLOCK POLYBAG.
- 3. LABEL ON POLYBAG TO READ AS FOLLOWS:  

621797-__	PART NO.
XX' DB25 M/M ALL LINE EXT.	XX' = LENGTH PER TABLE
- 4. THIS PRODUCT IS PRODUCED IN COMPLIANCE WITH ANSI/ASQC Z1.4-1993, TO AN INSPECTION LEVEL III, WITH A NORMAL SAMPLING PLAN.

#4-40 SLOTTED THUMBSCREW	4
OVERMOLD, PVC, BEIGE	3
CONNECTOR, DB25, MALE	2
CABLE, 25 CONDUCTOR	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.EISENTRAUT 11-20-96	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK D.WILSON 11-21-96		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.CAPP 11-21-96	NAME CABLE ASSY, DB25 MALE TO MALE, OVERMOLDED	
0 PLC ± -		PRODUCT SPEC	SIZE A2 CAGE CODE 00779 C=621797	
1 PLC ± -		APPLICATION SPEC	RESTRICTED TO	
2 PLC ± -		WEIGHT -	SCALE NTS SHEET 1 of 1 REV B	
3 PLC ± -		RESTRICTED CUSTOMER		
4 PLC ± -				
ANGLES ± -				
FINISH -				