


THREE COMPONENT, DRAIN WIRE, SHIELDED, WRAPPED AND JACKETED
AUTOMOTIVE SIGNAL CABLE.

The complete requirements for procuring the wire described herein shall consist of this document.



Part Number	Braid Size (AWG)	Braid Outer Diameter (mm)	Wrap Outer Diameter (mm)	Overall Diameter (mm)		Nominal Weight (kg/ km)	Copper Weight Information Only (gm/ m)
				Min.	Max.		
62CD003-1.00-*/*/*-0	36	4.2	4.3	5.3	5.7	68	51
62CD003-1.50-*/*/*-0	36	4.9	5.0	6.0	6.4	92	72

Note: All dimensions are nominal unless otherwise stated.

PERFORMANCE REQUIREMENTS: To be tested to and meet all the requirements of the issue in effect of Raychem Specification WSD 948 .

COLOUR CODE: The '*' in the part number shall be replaced by a standard colour code designator in accordance with Mil Std 681.
e.g. 62CD003-1.50-2/6/9-0 components red /blue/white, black jacket.

CABLE MARKING: Raychem-ASC-DW-XX-T3-125C-FIAT
XX = 3X Size
e.g. Raychem-ASC-DW-3X1.5-T3-125C-FIAT
Marking Interval shall be: ≤ 200 mm

ADDITIONAL REQUIREMENTS: Unless otherwise specified on the order this cable may be supplied in the following maximum number of continuous lengths.
Order Quantity(m)/ 100 + One other length

APPROVAL: Electronic sign off - no signatures will appear.