


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-	E1	REVISED PER ECO-11-005294	02APR11	RK HMR



LC CONN. SIDE MARK	LC CONN. SIDE MARK
A	B
B	A

NOTES:

- 1 ATTENUATION ≤ 0.3 dB, MEASURED AGAINST REFERENCE CONNECTOR
- 2 RETURN LOSS ≥ 45 dB, IN MATED CONDITION
- 3 TUNED CONNECTORS
- △4 INFORMATION ON CABLE LABEL:
 - UNIQUE SERIAL NUMBER
 - TE CONNECTIVITY PART NUMBER
 - PO NUMBER
 - ATTENUATION AND RETURN LOSS AT 1310 nm
- △5 BLANK LABEL
- 6 CABLE INFORMATION:
 - CORE DIAMETER: 9/125 μm
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: YELLOW
 - OUTER JACKET MATERIAL: LSZH
- △7 FOR LENGTHS < 60 cm SHORTER SLIT LENGTHS APPLY
- △8 DELIVERED ON A REEL IN A BOX

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850

PART NUMBER	"L" (meter)
X-6536501-Y	XY.0
8-6536501-1	200 -0/+10
8-6536501-2	100 -0/+3
8-6536501-3	125 -0/+6
8-6536501-6	0.25 -0/+0.05
9-6536501-0	0.5 -0/+0.1

Qty	Description	Item
2	BLANK LABEL	4
4	INFORMATION LABEL	3
2	LC DUPLEX CONNECTOR, SINGLE MODE, BLUE	2
L	FOCAB 1.8MZ 9/125, YELLOW LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R. COOLEN 01AUG2007		FOSM LEAD 1.8MZ LC/PC - LC/PC DUPLEX TUNED
CHK A. HENGELMOLEN 10AUG2007		
APVD A. HENGELMOLEN 10AUG2007		
PRODUCT SPEC		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME
0 PLC ± -	1 PLC ± -	SIZE
2 PLC ± -	2 PLC ± -	CAGE CODE
3 PLC ± -	3 PLC ± -	DRAWING NO
4 PLC ± -	4 PLC ± -	RESTRICTED TO
ANGLES ± -	FINISH	SCALE
MATERIAL	WEIGHT	SHEET
		1 OF 1
	CUSTOMER DRAWING	REV
		E1

6536501