


© - TE Connectivity. All Rights Reserved.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	F	REVISED PER ECN-22-138023	08FEB2022	RK DR



**AMP**  
WIRE RANGE

---

1/0 AWG  
STRANDED

- 1 STAMP AMP 1/0W\* APPROX AS SHOWN
- 2 NICKEL PLATE .000300 MIN EXT THK PER SAE AMS-QQ-N-290.
- 3 MATERIAL, COPPER PER ASTM B152, ANNEALED.
- 4. MATERIAL THICKNESS 1.778±.076 [0.076±.003]

50	LOOSE PIECE	696710-1
QTY	PACKAGE TYPE	PART NO

<b>CUSTOMER SERVICE SYSTEMS</b>		MAX RECOMMENDED OPERATING TEMPERATURE: 343°C [649°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 09MAR04	<b>STE</b> TE Connectivity					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M SPICER 09MAR04				NAME		
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] STRANDED			APVD M SPICER 09MAR04	PRODUCT SPEC 108-32046					
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			MATERIAL 3	FINISH 2	APPLICATION SPEC 114-2162	SIZE A3	CAGE CODE 00779	DRAWING NO C-696710	
					CUSTOMER DRAWING			RESTRICTED TO	SCALE 2:1	SHEET 1 OF 1	REV F