




REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	0	-	20AUG 97	JB	AD
	A	EQ00-0011-99	03FEB 99	DB	AD
	B	ECR-18-019748 (UPDATE MARKING PROCESS)	18DEC2018	BM	AG

BORNE PREISOLEE DE CONNEXION
BOLTED PREINSULATED CONNECTION



MARQUAGE : LOGO, REFERENCE, CAPACITE, LOT
Marking: Logo, reference, capacities, date



ENVELOPPE ISOLANTE (elastomere)
Insulated housing (elastomer)

TETE FUSIBLE ISOLANTE (plastique)
Insulated shear head (plastic)

BAGUE (elastomere)
Terminal seal (elastomer)

OBTURATEUR D'ETANCHEITE ET D'ISOLEMENT POUR POSITION DECONNECTEE
Insulated and watertight cap for disconnected position

PN	DESIGNATION	CAPACITES (mm ²) CAPACITIES	COTE TETE FUSIBLE (mm) DIMENSION SHEAR HEAD	COUPLE DE SERRAGE (Nm) TIGHTENING TORQUE
-	BPC 35M-35M	6 a 35M (version EDF)	13	10
719819-1	BPC 35-35	4 to 35 STR Alu or Cu	13	10

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES: -

FINISH
FINITION -

DIMENSIONS:

mm

DWN/DESSINE
D.BENOIT

03FEB 99

MATERIAL
MATIERE -

CHK/VERIFIE
F.BARANGER

APVD/APPROUVE
G.NEDELLEC

PRODUCT SPEC
SPEC. PRODUIT -

APPLICATION SPEC
SPEC. APPLICATION -

WEIGHT
MASSE APPROX. 81.5 g.

NAME
TITRE

ENSEMBLE BPC
ASSEMBLY BPC

SIZE
FORMAT

A4

CAGE CODE

00779

DRAWING NO
No PLAN

C-719819

RESTRICTED TO
RESERVE A

-

CUSTOMER DRAWING

/PLAN CLIENT

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE 7:10

SHEET
FEUILLE

OF
DE 1

REV

B

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

ALL RIGHTS RESERVED.
TOUS DROITS RESERVES.

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE AMP

© COPYRIGHT copyright_d8Ye-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES:
(SUIV NB DE DECIMALES):

0 PLC/DEC: ±0
1 PLC/DEC: ±0
2 PLC/DEC: ±0
3 PLC/DEC: ±0
4 PLC/DEC: ±0.0001
ANGLES ±-

