


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	, 19
© COPYRIGHT 19		BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.	

		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	7470955
	✓		A	REDRAWN	7-23-80	-



- ① BRIGHT NICKEL OVER BRIGHT COPPER, ALL SURFACES.
- ② SELECTIVE PLATED ON INNER SURFACES ONLY WITH NICKEL OVER COPPER.

OBSOLETE		B	.225	1-747095-2
		E	.300	1-747095-1
		H	.375	1-747095-0
		K	.430	747095-9
		B	.225	747095-4
		E	.300	747095-3
		H	.375	747095-2
		K	.430	747095-1
FINISH		SIZE IDENT LETTER	CABLE DIA	PART NUMBER

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON
2 PLC DEC $\pm$ -
3 PLC DEC $\pm$.005
ANGLES $\pm$ -

MATERIAL
FLAME RETARDANT
THERMOPLASTIC ABS

FINISH
SEE DASH NUMBERS

DR 7-23-90
J GALLUCCI BG

CHK 22 " 9-10-90

J. Mullins

APPD *[Signature]* 9-10-90

APPD -

PRODUCT SPEC 4/11/90

PRODUCT SPEC

APPLICATION SPEC

APPLICATION SPEC

AMP AMP INCORPORATED
Harrisburg, Pa. 17105

NAME	CABLE CLAMP, SIZE 2, 180°, AMPLIMITE™ SERIES, PLATED PLASTIC
------	--

SIZE	FSCM NO	DRAWING NO
C	00779	747095

SCALE	2:1	SHEET	1 OF 1
-------	-----	-------	--------

AMP 1471-6 REV 3-88

23 AUG 1990 10:01:05 AMPT0842

<140285>DT 4023<L STONES/UT4>L STONES.R027

CUSTOMER DRAWING