




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .  
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

| LOC | DIST | P | F | REVISIONS |     |                             |         |      |
|-----|------|---|---|-----------|-----|-----------------------------|---------|------|
|     |      |   |   | ZONE      | LTR | DESCRIPTION                 | DATE    | APPD |
| GP  | 00   |   |   |           | A   | REVISED PER EC 0513-0160-03 | 23MAY03 | JG   |



- 1 CARBON STEEL PER ASTM A 109.
- 2 1.27µm [ .000050 ] MIN BRIGHT TIN-LEAD OVER  
1.27µm [ .000050 ] MIN NICKEL.
- 3 1.27µm [ .000050 ] MIN BRIGHT TIN OVER  
1.27µm [ .000050 ] MIN NICKEL.

|                                                                                                                                                  |                          |                                                                        |  |              |  |
|--------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|------------------------------------------------------------------------|--|--------------|--|
|                                                                                                                                                  |                          | FINISH                                                                 |  | PART NO      |  |
| DO NOT SCALE PRINT.<br>UNLESS SPECIFIED<br>DIMENSIONS IN mm [INCHES]<br>TOLERANCES ON:<br>2 PLC DEC ± 0.13 [.005]<br>3 PLC DEC ± -<br>ANGLES ± - | DR 02/19/91<br>C.OBERMAN | <div>AMP</div> AMP Incorporated<br>Harrisburg, PA 17105-3608           |  |              |  |
|                                                                                                                                                  | CHK -<br>-               |                                                                        |  |              |  |
|                                                                                                                                                  | APPD -<br>-              | NAME<br>STRAIN RELIEF, STAPLE, 72-120<br>POSN, .050 SERIES, AMPLIMITE™ |  |              |  |
|                                                                                                                                                  | APPD -<br>-              |                                                                        |  |              |  |
| MATERIAL<br><div>1</div>                                                                                                                         | PRODUCT SPEC<br>-        | SIZE<br>B<br>CAGE CODE<br>00779<br>DRAWING NO<br>749125                |  |              |  |
|                                                                                                                                                  | APPLICATION SPEC<br>-    |                                                                        |  |              |  |
| FINISH<br><br>SEE TABLE                                                                                                                          | WEIGHT -                 | SCALE 4:1                                                              |  | SHEET 1 OF 1 |  |