

2				015T	<u>+</u>
PFZONEL				ROVED	•
	O RLSD PER	TTI 85-50	6/12/85 13/		
V V	REV PER EC		7/16/85 DM	IR5	
	B REV PER CM-C	626	6286 Xul,	RS	
	C REVISED PER C1 REVISED PER ECR-2		7-12-20 PC 200CT2021 PJ	R5 VS	
				D	
PARTS COMPLY SPEC 109-11-3.	WITH AMP	SOLDERAB	ILITY		
RECOMMENDED Reflow solde				4.	
MATERIAL-HOU CON	ISING: NYLON	N, UL94V-2 RZ (PRE-TI	(NATUR IN).	AL)	
.010 MIN THICK	SOLDER PA	ASTE, 63/37	TIN-LEAD	S.	
PINS TO BE HEA CONNECTOR T		TO RETAI	N		
DIMENSION SHOWN REPRI GROWTH DUE TO END USE SHOULD BE ACCOUNTED F	E LOCATION MOISTUR			1	
				4	
	•				
	-	•			
	· .				
	-21			В	
<u> </u>					
•				[-
				ŀ	
	770149-1 9	SHOWN		F	
			<u>1</u>		
TRACT NO	T			T NO	
		TE Conn	nectivity	F	
Beck 6/12/85	NAME PIN HE	ADER ASSE	EMBLY	/ ,	4
PD (1) 7-16-85	RIGHT /	ANGLE MO	UNT 34	CKT,	
PD	COMME	RCIAL MA	TE-N-L	ok	
GN APPD	SIZE FSCM NO	DRAWING NO			
HER APPD	D 00779	77	70149		
	SCALE 4:1		SHEET -		
		CUSTOM	ER DRA	WING	
		1		······	