





D

C

B

A



- 1

MATERIAL;
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS.
HOLDDOWNS - PHOSPHOR BRONZE.
- 2

DIMENSION APPLIES TO SOLDERTAIL SURFACES, HOLDDOWNS SURFACES AND STANDOFF SURFACES.
- 3

RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 4

ALL SOLDERTAILS AND HOLDDOWNS.
- 5

PLATING;
CONTACTS - 0.38µm MINIMUM GOLD ON MATING AREA.
2.54µm MINIMUM MATTE TIN ON SOLDER TAIL.
ALL OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 6

COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 7

FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	36.86	40.27	33.00	40.00	24	5-794628-4
	33.86	37.27	30.00	37.00	22	5-794628-2
	30.86	34.27	27.00	34.00	20	5-794628-0
	27.86	31.27	24.00	31.00	18	4-794628-8
OBSOLETE	24.86	28.27	21.00	28.00	16	4-794628-6
OBSOLETE	21.86	25.27	18.00	25.00	14	4-794628-4
	18.86	22.27	15.00	22.00	12	4-794628-2
	15.86	19.27	12.00	19.00	10	4-794628-0
	12.86	16.27	9.00	16.00	8	3-794628-8
	9.86	13.27	6.00	13.00	6	3-794628-6
	6.86	10.27	3.00	10.00	4	3-794628-4
OBSOLETE	3.86	7.27		7.00	2	3-794628-2
	DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

K. WHITAKER

19MAR2003

CHK

C. JONES

19MAR2003

APVD

C. JONES

19MAR2003

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±

1 PLC

±

2 PLC

±0.20

3 PLC

±

4 PLC

±

ANGLES

±1°

FINISH

1

5

PRODUCT SPEC

108-1836

APPLICATION SPEC

114-13000

WEIGHT

-

CUSTOMER DRAWING

NAME

TE Connectivity

SURFACE MOUNT, RIGHT ANGLE, SURFACE MOUNT HOLDDOWN, ASSEMBLY, 15 GOLD HEADER, DUAL ROW, MICRO MATE-N-LOK™

SIZE

A2

CAGE CODE

0779

DRAWING NO

C-794628

RESTRICTED TO

-

SCALE

4:1

SHEET

1

OF

2

REV

H7

