




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E5	REVISED PER ECN-24-279340	20AUG2024	WLS	JP



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP. , NYLON, COLOR BLACK.
CONTACT - BRASS.
 - 2 MAXIMUM INSERTION 30 LBS.
 - 3 RECOMMENDED BOARD THICKNESS 1.57.
 - 4 FINISHING: CONTACT - 0.38 μ m MINIMUM GOLD ON MATING AREA.
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS.
ALL OVER 1.27 μ m MINIMUM NICKEL.
 - 5 CUTTING AREA REGION, NO PLATING IS PRESENT.
- 6 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 7 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	40.00	33.00	36.86	24	5-794631-4
	37.00	30.00	33.86	22	5-794631-2
OBSOLETE	34.00	27.00	30.86	20	5-794631-0
OBSOLETE	31.00	24.00	27.86	18	4-794631-8
	28.00	21.00	24.86	16	4-794631-6
	25.00	18.00	21.86	14	4-794631-4
	22.00	15.00	18.86	12	4-794631-2
	19.00	12.00	15.86	10	4-794631-0
	16.00	9.00	12.86	8	3-794631-8
	13.00	6.00	9.86	6	3-794631-6
	10.00	3.00	6.86	4	3-794631-4
	7.00	-	3.86	2	3-794631-2
	DIM Y	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 16AUG99 CHK K. COBLE 16AUG99		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.20 3 PLC ±. 4 PLC ±. ANGLES ±°		NAME VERTICAL HEADER ASSEMBLY, THRU HOLE, 15 GOLD, DUAL ROW, MICRO MATE-N-LOK TM			
		APVD K. COBLE 16AUG99 PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000		SIZE A2		CAGE CODE 00779	
MATERIAL 		FINISH 		DRAWING NO C=794631		RESTRICTED TO -	
		WEIGHT -					
CUSTOMER DRAWING						SCALE 4:1	
						SHEET 1 OF 2	
						REV E5	

