
	8		7		6
	THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION ALL RIGHTS RESERVED.	19		
D					
			45° 2 PLC		
			2 PLC		
С					M
					20.83 REF. [.820]
			<	- 20 57 REE	
				- 20.57 REF	
В					
				\mathcal{A}	
	(C)		66		
	Į.				
A					
<i>רו</i>		3 - 1	DIMENSIONAL MODEL SCALE 4:I		


4805 (3/13)


5	4	3	





3 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.





THIS DRAWING IS A C	ONTROLLED DOCUMENT.
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±- 1 PLC ±- 2 PLC ±0.13[.005] 3 PLC ±- 4 PLC ±- ANGLES ±0°30
MATERIAL NYLON, UL 94V-2	FINISH -
-	-

\cap	
1	
L	

		REVISIONS			
Ρ	LTR	DESCRIPTION	DATE	DWN	APVD
	А	REVISED PER OG3B-0550-01	02-OCT-0I	ΚW	SR
	ΑI	REVISED PER ECO-07-001375	18JAN2007	ΚW	DC
	A 2	REV. BY ECO 17-011267	24AUG2017	НC	KR
	A 3	REVISED PER ECR-17-014951	160CT2017	BDA	K R

1

four ribs equally spaced, no specific orientation.

2 csa certification logo located approximately as shown.

0. 72 N ³	BLACK	794911-9
0. 72 N ³	G R A Y	794911-8
0.172 IN ³	BROWN	794911-7
0.172 IN ³	BLUE	794911-6
0.172 IN ³	GREEN	794911-5
0.172 IN ³	YELLOW	7949 -4
0.172 IN ³	ORANGE	794911-3
0.172 IN ³	R E D	794911-2
0.172 IN ³	NATURAL	7949 -
VOLUME	COLOR	PART NUMBER

CONTROLLED DOCUMENT. DWN 23-MAR-2001 K. WHITAKER CHK 23-MAR-2001	TE Connectivity
TOLERANCES UNLESS OTHERWISE SPECIFIED: S. RIDGILL 0 PLC ±- PRODUCT SPEC 1 PLC ±- - 2 PLC ±0.13[.005] - 3 PLC ±- APPLICATION SPEC	PLUG, CIRCULAR, 6 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)
4 PLC ±- ANGLES ±0°30′	SIZE CAGE CODE DRAWING NO
FINISH WEIGHT _	A 1 00779 C=794911 -
- CUSTOMER DRAWING	SCALE 4: SHEET OF REVA3

В