


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECN-24-293317	13NOV2024	RK	FJS



1. THIS PART WILL ACCEPT FOUR (4) MULTIMATE PIN CONTACTS.


2. HOUSING AND PRESSURE PLATE: NYLON, BLACK.

PERIPHERAL SEAL: ELASTOMER, BLACK.

WIRE ENTRY SEAL: ELASTOMER, RED-IRON OXIDE.

THREADED INSERTS: BRASS

#4-40 THREADED INSERTS	796095-5
Ø3.18 (.125) HOLES	796095-2
MOUNTING FEATURES	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.DORWART 25 SEP 98	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK R.WALTER 25 SEP 98					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.WALTER 25 SEP 98	NAME RECEPTACLE ASSY, 11-4, STD SEX, SERIES I, SEALED, CIRCULAR PLASTIC CONNECTOR			
			PRODUCT SPEC				
			APPLICATION SPEC				
MATERIAL -	FINISH -		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=796095	RESTRICTED TO -
	CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV B1	